


FLOW^{EVO}

Infrared gas sensor CH₄ // Methane // 2.5 Vol.-% // (also applicable for CH₃Br // Bromomethane // Appr. 6 Vol.-%)
 smartGAS item number: F3-042256-05004



*Illustration similar (gold coated)

- Pre calibrated
- Compact design
- 3/5 mm gas line connectors
- 3.3 – 6.0 V DC supply voltage
- Modbus ASCII or RTU
- Status indication by LED
- Low drift

Non Dispersive Infrared (NDIR) gas sensor for gas analysis using dual wavelength technology.
 Designed for process control of CH₄ or (using a correction factor of ~ 2.3) also applicable for fumigation control (CH₃Br). The special gold coated sample cell protects the sensor against corrosion or wearing of the optical surfaces.

The FLOW^{EVO} sensor can easily be integrated into OEM systems, where long term stability, repeatability and reliable performance are required. It can be used for stack gas monitoring, in incineration plants but also for fumigation processes and container transport. High-precision NDIR technology requires little maintenance compared to conventional chemical sensors and its small detection limits and long life expectancy qualify our NDIR sensors for numerous tasks in countless areas of scientific research.

APPLICATION EXAMPLES

FUMIGATION MONITORING of CH₃Br
PROCESS CONTROL of CH₄

FLOW^{EVO}

Infrared gas sensor CH₄ // Methane // 2.5 Vol.-% // (also applicable for CH₃Br // Bromomethane // Appr. 6 Vol.-%)
 smartGAS item number: F3-042256-05004

General features	
Measurement principle:	Non Dispersive Infra-Red (NDIR), dual wavelength
Measurement range:	0..2.5 Vol.-% Full Scale (FS)
Gas supply:	by flow (nearly atmospheric pressure)
Flow rate:	0.1 .. 1.0 l / min
Dimensions:	113 mm x 30 mm x 36 mm (L x W x H)
Warm-up time:	< 2 minutes (start up time) < 30 minutes (full specification)
Measuring response*	
Response time (t ₉₀):	Appr. 12 s @ 0.7 l / min
Digital resolution (@ zero):	0.001 Vol.-%
Detection limit (3 σ):	≤ 0.015 Vol.-%
Repeatability:	≤ ± 0.03 Vol.-%
Linearity error (straight line deviation):	≤ ± 0.04 Vol.-%
Long term stability (span):	≤ ± 0.05 Vol.-% over 1000 h period
Long term stability (zero):	≤ ± 0.05 Vol.-% over 1000 h period
Influence of T, P, flow rate, other*	
Temp. dependence (zero):	≤ ± 0.01 Vol.-% per °C
Temp. dependence (span):	≤ ± 0.01 Vol.-% per °C
Pressure dependence:	+ 0.1 % of measured value / hPa
Flow rate dependence:	≤ ± 0.02 Vol.-% per 0.1 l / min
Cross sensitivity (zero) other gases:	Appr. 2.5 Vol.-% @ 5.8 Vol.-% CH ₃ Br in dry air
Electrical inputs and outputs	
Supply voltage:	3.3 V .. 6.0 V DC
Supply current (peak):	< 400 mA @ 3.3 V, < 240 mA @ 5.0 V
Inrush current:	< 600 mA
Average power consumption:	< 800 mW
Digital output signal:	Modbus ASCII / RTU via UART, autobaud, autoframe
Calibration:	zero and span by SW
Climatic conditions	
Operating temperature:	0 .. + 50 °C
Storage temperature:	-20 .. + 60 °C
Air pressure:	800 .. 1150 hPa
Ambient humidity:	0 .. 95 % relative humidity (not condensing)
* Typical values related to 1013 hPa, Ta=22 °C, flow = 0.7 l / min for dry (not condensing) and clean sample gas. Stated values exclude calibration gas tolerance.	

All rights reserved. Any logos and/or product names are trademarks of smartGAS. The reproduction, transfer, distribution or storage of information contained in this brochure in any form without the prior written consent of smartGAS is strictly prohibited. All specifications – technical included – are subject to change without notice. Depending on the application, the target gas and the measurement range the technical data may differ. No liability is accepted for any consequential losses, injury or damage resulting from the use of this document or from any omissions or errors herein. The data is given for guidance only. It does not constitute a specification or an offer for sale.

For more information, please visit www.smartgas.eu or contact us at sales@smartgas.eu

Please consult smartGAS sales for parts specified with other temperature and measurement ranges.

At first initiation and depending on application and ambient conditions recalibration is recommended. Recurring cycles of recalibration are recommended.

Headquarter Switzerland:
Angst+Pfister Sensors and Power AG

Thurgauerstrasse 66
CH-8050 Zurich
Phone +41 44 877 35 00
sensorsandpower@angst-pfister.com

Office Germany:
Angst+Pfister Sensors and Power
Deutschland GmbH
Edisonstraße 16
D-85716 Unterschleißheim
Phone +49 89 374 288 87 0
sensorsandpower.de@angst-pfister.com



We are here for you. Addresses and Contacts.

Sales Germany & Austria

Geometrical sensors
Other products

Kurt Stritzelberger
Phone +49 89 374 288 87 22
kurt.stritzelberger@angst-pfister.com

Pressure sensors
Other products

Gerhard Vetter
Phone +49 89 374 288 87 26
gerhard.vetter@angst-pfister.com

Gas sensors and modules

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Switzerland & Liechtenstein

Postcode 3000 – 9999

Basil Frei
Phone +41 44 877 35 18
basil.frei@angst-pfister.com

Postcode 1000 – 2999

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Sales International Key Accounts

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Other Countries / Product Management

Pressure Sensors
Load Cells

Philipp Kistler
Phone +41 44 877 35 03
philipp.kistler@angst-pfister.com

Gas sensors
Gas sensor modules

Dr. Thomas Clausen
Phone +49 89 374 288 87 24
thomas.clausen@angst-pfister.com

Flow / Level / Medical products

Dr. Adriano Pittarelli
Phone +49 89 374 288 87 67
adriano.pittarelli@angst-pfister.com

Power supplies

Sebastiano Leggio
Phone +41 44 877 35 06
sebastiano.leggio@angst-pfister.com

Linear position sensors
Angle sensors

Eric Letsch
Phone +41 44 877 35 14
eric.letsch@angst-pfister.com

Accelerometers
Sensor elements

Christoph Kleye
Phone +49 89 374 288 87 61
christoph.kleye@angst-pfister.com

Drive technology
CH Postcode 5000 – 9999 / DE

Roman Homa
Phone +41 76 444 00 86
roman.homa@angst-pfister.com

Drive technology
CH Postcode 1000 – 4999 / AT / IT / FR

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Harald Thomas
Phone +49 89 374 288 87 23
harald.thomas@angst-pfister.com