

FLOW^{EVO} for Biogas application

Infrared gas sensor CO₂ // Carbon dioxide // 100 Vol.-%
 smartGAS item number: F3-214108-05000



- Pre calibrated
- Compact design
- 3/5 mm gas line connectors
- 3.3 – 6.0 V DC supply voltage
- Modbus ASCII or RTU
- Status indication by LED
- Low drift

Non Dispersive Infrared (NDIR) gas sensor for process control and gas analysing using dual wavelength technology. Designed for process control, lab analysing and environmental monitoring in a wide range of gas measurement systems.

The FLOW^{EVO} CO₂ sensor can easily be integrated into OEM systems, where long term stability, repeatability and reliable performance are required. Based on robust and precise NDIR technology our CO₂ sensors offer enduring solutions in the area of controlled combustion and process control. Furthermore, they can be used in environmental analysis and various other fields of scientific research where low signal drift and high selectivity are crucial for exact measurements and subsequent processing.

Modbus ASCII or RTU data communication offer a variety of options to connect the FLOW^{EVO} sensor to a controller.

APPLICATION EXAMPLE

GAS ANALYSING
 PROCESS CONTROL
 BIOGAS APPLICATION
 RESEARCH

FLOW^{EVO} for Biogas application

Infrared gas sensor CO₂ // Carbon dioxide // 100 Vol.-%
 smartGAS item number: F3-214108-05000

General features	
Measurement principle:	Non Dispersive Infra-Red (NDIR), dual wavelength
Measurement range:	0..100 Vol.-% Full Scale (FS)
Gas supply:	by flow (nearly atmospheric pressure)
Flow rate:	0.1 .. 1.0 l / min
Dimensions:	76 mm x 30 mm x 37 mm (L x W x H)
Warm-up time:	< 2 minutes (start up time) < 30 minutes (full specification)
Measuring response	related to Pa = 1013 hPa, Ta = 25 °C, flow = 0.7 l / min
Response time (t ₉₀):	Appr. 12 s @ 0.7 l / min
Digital resolution (@ zero):	0.01 Vol.-%
Detection limit (3 σ):	≤ 0.2 Vol.-%
Repeatability:	≤ ± 0.6 Vol.-%
Linearity error (straight line deviation):	≤ ± 0.9 Vol.-%
Long term stability (span):	≤ ± 2.0 Vol.-% over 1000 h period
Long term stability (zero):	≤ ± 1.0 Vol.-% over 1000 h period
Influence of T, P, flow rate, other	related to Pa = 1013 hPa, Ta = 25 °C, flow = 0.7 l / min
Temp. dependence (zero):	≤ ± 0.1 Vol.-% per °C
Temp. dependence (span):	≤ ± 0.2 Vol.-% per °C
Pressure dependence:	+ 0.156 % of measurement value / hPa
Flow rate dependence:	≤ ± 0.01 Vol.-% per 0.1 l / min
Cross sensitivity (zero) other gases:	consult factory
Electrical inputs and outputs	
Supply voltage:	3.3 V .. 6.0 V DC
Supply current (peak):	< 400 mA @ 3.3 V, < 240 mA @ 5.0 V
Inrush current:	< 600 mA
Average power consumption:	< 800 mW
Digital output signal:	Modbus ASCII / RTU via UART, autobaud, autoframe
Calibration:	zero and span by SW
Climatic conditions	
Operating temperature:	0 .. + 50 °C
Storage temperature:	-20 .. + 60 °C
Air pressure:	800 .. 1150 hPa
Ambient humidity:	0 .. 95 % relative humidity (not condensing)
* Typical values related to 1013 hPa, Ta=22 °C, flow = 0.7 l / min for dry (not condensing) and clean sample gas. Stated values exclude calibration gas tolerance.	

All rights reserved. Any logos and/or product names are trademarks of smartGAS. The reproduction, transfer, distribution or storage of information contained in this brochure in any form without the prior written consent of smartGAS is strictly prohibited. All specifications – technical included – are subject to change without notice. Depending on the application, the target gas and the measurement range the technical data may differ. No liability is accepted for any consequential losses, injury or damage resulting from the use of this document or from any omissions or errors herein. The data is given for guidance only. It does not constitute a specification or an offer for sale.

For more information, please visit www.smartgas.eu or contact us at sales@smartgas.eu

Please consult smartGAS sales for parts specified with other temperature and measurement ranges.

At first initiation and depending on application and ambient conditions recalibration is recommended. Recurring cycles of recalibration are recommended.

Headquarter Switzerland:
Angst+Pfister Sensors and Power AG

Thurgauerstrasse 66
CH-8050 Zurich
Phone +41 44 877 35 00
sensorsandpower@angst-pfister.com

Office Germany:
Angst+Pfister Sensors and Power
Deutschland GmbH
Edisonstraße 16
D-85716 Unterschleißheim
Phone +49 89 374 288 87 0
sensorsandpower.de@angst-pfister.com



We are here for you. Addresses and Contacts.

Sales Germany & Austria

Geometrical sensors
Other products

Kurt Stritzelberger
Phone +49 89 374 288 87 22
kurt.stritzelberger@angst-pfister.com

Pressure sensors
Other products

Gerhard Vetter
Phone +49 89 374 288 87 26
gerhard.vetter@angst-pfister.com

Gas sensors and modules

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Switzerland & Liechtenstein

Postcode 3000 – 9999

Basil Frei
Phone +41 44 877 35 18
basil.frei@angst-pfister.com

Postcode 1000 – 2999

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Sales International Key Accounts

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Other Countries / Product Management

Pressure Sensors
Load Cells

Philipp Kistler
Phone +41 44 877 35 03
philipp.kistler@angst-pfister.com

Gas sensors
Gas sensor modules

Dr. Thomas Clausen
Phone +49 89 374 288 87 24
thomas.clausen@angst-pfister.com

Flow / Level / Medical products

Dr. Adriano Pittarelli
Phone +49 89 374 288 87 67
adriano.pittarelli@angst-pfister.com

Power supplies

Sebastiano Leggio
Phone +41 44 877 35 06
sebastiano.leggio@angst-pfister.com

Linear position sensors
Angle sensors

Eric Letsch
Phone +41 44 877 35 14
eric.letsch@angst-pfister.com

Accelerometers
Sensor elements

Christoph Kleye
Phone +49 89 374 288 87 61
christoph.kleye@angst-pfister.com

Drive technology
CH Postcode 5000 – 9999 / DE

Roman Homa
Phone +41 76 444 00 86
roman.homa@angst-pfister.com

Drive technology
CH Postcode 1000 – 4999 / AT / IT / FR

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Harald Thomas
Phone +49 89 374 288 87 23
harald.thomas@angst-pfister.com