

Oxygen sensor module

FCX-M Data sheet

■ Features

- High accuracy
- Long life (More than 3 years in normal air) *1
- Continues calibration and maintenance not required *2
- Calibration gas not required
- From ppm to 95%O₂, wide measurement range
- No interference to media
- No pressure dependence

■ Applications

- Oxygen concentrator
- Nitrogen purifier
- Alarm for oxygen shortage
- Culture oven or Incubator
- Food packaging, preservation & logistics
- Combustion control
- Soldering system



■ Specifications

Item	Unit	FCX					
		-MP-F-AC	-MQ-F-AC	-MV-F -MV-F-AC	-MW-F -MW-F-AC	-MWGP-2A-F	-MEP2-F -MEP2-F-AC
Measurement range	%O ₂	50~1000 *3	0.05~1.0 %O ₂	0.1~25 %O ₂	0.1~95 %O ₂	75~95 %O ₂	0.1~25 %O ₂
Accuracy	%FS	±5.0		±1.0	±0.5	±2.0	±1.0
Response time *4	secs.	90		30			
Output	mV	50~1000 mV		0~250 mV	1~2700 mV	1235~2700 mV	4~20 *5
		$= \frac{999.5 \times 10^3}{\ln \left[1 - \frac{O_2\%}{10^6} \right]} \times$	$= \frac{99.5 \times 10^3}{\ln \left[1 - \frac{O_2\%}{100} \right]} \times$	$= -891 \times \ln \left[1 - \frac{O_2\%}{100} \right]$			$\ln \left[1 - \frac{O_2\%}{10^6} \right] + 4$
Power supply *6	VDC	5±0.2			5+0.1/-0.25		12±3
Power consumption	W	5			4		3
Operating temperature	°C	-10~50			0~60		-10~50
Operating humidity *7	%RH	0~85					
Dimensions(wXhXl)	mm	50 x 16 x 104			80 x 23 x 80/40		45 x 20 x 52
Weight	grams	65					40

Item	Unit	FCX	
		-MVL-F -MVL-F-AC	-MWL-F -MWL-F-AC
Measurement range	%O ₂	0.1~25 %O ₂	0.1~95 %O ₂
Accuracy	%FS	±1.0	±0.5
Response time *4	secs.	30	
Output	mV	1~250 mV	1~950 mV
		$= 10 \times O_2\%$	
Power supply *6	VDC	5±0.2	
Power consumption	W	5	
Operating temperature	°C	-10~50	
Operating humidity *7	%RH	0~85	
Dimensions(wXhXl)	mm	50 x 38 x 104	
Weight	grams	120	

*1: Depends on operating environment.

*2: Annual calibration or maintenance still recommended.

*3: ppm

*4: From 10 to 90% step change.

*5: mA

*6: Regulated DC power supply. The current capacity must be 1A.

*7: Without vapour condensation.

Note ; Please read above instructions before using the sensor.
Fujikura reserves right to change specifications without notice.

If you have any questions regarding technical issues or specifications,
please contact us.

Fujikura Ltd. Sensor Engineering Department
5-1 Kiba 1-chome, Koto-ku, Tokyo 135-8512, Japan
Phone +81-(0)3-5606-1072 E-mail : sensor@fujikura.co.jp

Instruction for use ;

- Sensor modules are calibrated with N₂-O₂ balance gases. Other gases may affect the sensor performance by increase errors.
- Do NOT separate the sensing element from the circuit board and lead wires length must be remained unchanged.
- Do NOT use in harsh environmental conditions containing halogen atoms(F,Cl,Br) , SO_x ,Nox or H₂S which make the sensor inferior in a short time.
- Flammable gases ,such as H₂ ,CO ,methane or Alcohol make a big error. And please note that the temperature at the sensing part goes up to 450 degrees C during the operation, which may exceed the flash point and cause explosion.
- Silicone gas or vapour including Siloxane also make the sensor inferior in a short time.
- Dust or oil mist cause failures of the products, errors or a slow response. They must be eliminated with a filter.
- Water drop's contact may give a damage to sensor. It must be eliminated with a filter.
- Temperature at the sensor mesh surface reach 50~80 degrees C during operation. Please take precautions against burning yourself.
- A strong shock such as drop may cut internal wires or break the sensor pellet which is made of ceramic. Do NOT apply a shock of 10G or more to the sensor.
- The warranty period is one year from the ex-factory date. This warranty does NOT apply to the sensors as follows ;
 - There are any defects to faults caused by an improper dealing during the transportation after Fujikura has delivered the sensor to place where the buyer had instructed.
 - There are any defects or faults caused by the buyer's misuses ,abuse or neglect.
 - The buyer fixed or remake the sensors.
 - There are any identical or consequential damages which are given in the usage.
 - There are any defects or faults caused by natural disasters such as life ,earthquake, flood or thunder.
- Fujikura's oxygen sensors are NOT developed ,designed ,manufactured ,sold ,intended or authorized for use as components in systems intended for the surgical implant into the body ,other applications intended to support or sustain life ,fail-safe applications in which the failures ,breakages or where misused of the sensors could create a situation where personal injury or death ,explosion or fire ,or serious social damage may occur. Fujikura and its subcontractors and distributors accept NO responsibility the buyer's selection and use of Fujikura's oxygen sensors without Fujikura's written approval in any such unintended or unauthorized and situation where personal injury or death ,explosion or fire ,or serious social damage may occur.
- A fail-safe design is strongly required when customers use the sensor in medical applications or alarm systems for oxygen shortage even except above.

"Tsunagu" Technology
Fujikura

Headquarter Switzerland:
Angst+Pfister Sensors and Power AG

Thurgauerstrasse 66
CH-8050 Zurich
Phone +41 44 877 35 00
sensorsandpower@angst-pfister.com

Office Germany:
Angst+Pfister Sensors and Power
Deutschland GmbH
Edisonstraße 16
D-85716 Unterschleißheim
Phone +49 89 374 288 87 0
sensorsandpower.de@angst-pfister.com



We are here for you. Addresses and Contacts.

Sales Germany & Austria

Geometrical sensors
Other products

Kurt Stritzelberger
Phone +49 89 374 288 87 22
kurt.stritzelberger@angst-pfister.com

Pressure sensors
Other products

Gerhard Vetter
Phone +49 89 374 288 87 26
gerhard.vetter@angst-pfister.com

Gas sensors and modules

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Switzerland & Liechtenstein

Postcode 3000 – 9999

Basil Frei
Phone +41 44 877 35 18
basil.frei@angst-pfister.com

Postcode 1000 – 2999

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Sales International Key Accounts

Peter Felder
Phone +41 44 877 35 05
peter.felder@angst-pfister.com

Sales Other Countries / Product Management

Pressure Sensors
Load Cells

Philipp Kistler
Phone +41 44 877 35 03
philipp.kistler@angst-pfister.com

Gas sensors
Gas sensor modules

Dr. Thomas Clausen
Phone +49 89 374 288 87 24
thomas.clausen@angst-pfister.com

Flow / Level / Medical products

Dr. Adriano Pittarelli
Phone +49 89 374 288 87 67
adriano.pittarelli@angst-pfister.com

Power supplies

Sebastiano Leggio
Phone +41 44 877 35 06
sebastiano.leggio@angst-pfister.com

Linear position sensors
Angle sensors

Eric Letsch
Phone +41 44 877 35 14
eric.letsch@angst-pfister.com

Accelerometers
Sensor elements

Christoph Kleye
Phone +49 89 374 288 87 61
christoph.kleye@angst-pfister.com

Drive technology
CH Postcode 5000 – 9999 / DE

Roman Homa
Phone +41 76 444 00 86
roman.homa@angst-pfister.com

Drive technology
CH Postcode 1000 – 4999 / AT / IT / FR

Christian Mohrenstecher
Phone +41 76 444 57 93
christian.mohrenstecher@angst-pfister.com

Harald Thomas
Phone +49 89 374 288 87 23
harald.thomas@angst-pfister.com